

AIR TURQUOISE SA | PARA-TEST.COM

Route du Pré-au-Comté 8 ▲ CH-1844 Villeneuve ▲ +41 (0)21 965 65 65

Test laboratory for paragliders, paraglider harnesses
and paraglider reserve parachutes



Classification: **A**

In accordance with standards EN 926-1:2015, EN 926-2:2013+A1:2021 and NfL 2-565-20

Date of issue (DMY):

Manufacturer:

Model:

Serial number:

PG_2019.2022

09.12.2022

AirDesign GmbH

SUSI 4 18

XS23181PP2206007P

Configuration during flight tests

Paraglider

Maximum weight in flight (kg)	72
Minimum weight in flight (kg)	50
Glider's weight (kg)	2.6
Number of risers	3+1
Projected area (m2)	16.17

Accessories

Range of speed system (cm)	15.6
Speed range using brakes (km/h)	13
Total speed range with accessories (km/h)	27
Range of trimmers (cm)	0

Harness used for testing (max weight)

Harness type	ABS
Harness brand	Woody Valley
Harness model	Wani Light 2 M
Harness to risers distance (cm)	43
Distance between risers (cm)	40

Inspections (whichever happens first)

After 24 months or 100 flight hours (whichever occurs first)
Warning! Before use refer to user's manual
Person or company having presented the glider for testing: None

1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23
A 0

AIR TURQUOISE SA | PARA-TEST.COM

Route du Pré-au-Comté 8 ▲ CH-1844 Villeneuve ▲ +41 (0)21 965 65 65

Test laboratory for paragliders, paraglider harnesses
and paraglider reserve parachutes



Classification: **B**

In accordance with standards EN 926-1:2015, EN 926-2:2013+A1:2021 and NfL 2-565-20

Date of issue (DMY):

Manufacturer:

Model:

Serial number:

PG_2019.2022

09.12.2022

AirDesign GmbH

SUSI 4 18

XS23181PP2206007P

Configuration during flight tests

Paraglider

Extended weight in flight (kg)	90
Minimum weight in flight (kg)	50
Glider's weight (kg)	2.6
Number of risers	3+1
Projected area (m2)	16.17

Accessories

Range of speed system (cm)	15.6
Speed range using brakes (km/h)	13
Total speed range with accessories (km/h)	27
Range of trimmers (cm)	0

Harness used for testing (max weight)

Harness type	ABS
Harness brand	Advance
Harness model	Success 4 M
Harness to risers distance (cm)	43
Distance between risers (cm)	44

Inspections (whichever happens first)

After 24 months or 100 flight hours (whichever occurs first)
Warning! Before use refer to user's manual
Person or company having presented the glider for testing: None

1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23
A A B A A A A A A A A B B A A A A A A A 0